

CERTIFICATE OF ANALYSIS

12X 835M30 (batch A)

Certified Reference Material Information

Type: LOW-ALLOY STEEL (WROUGHT)
Form and Size: Disc, 45mm diameter
Manufactured by: Gerdau, Spain
Certified and Supplied by: MBH Analytical Ltd

Assigned Values

Percentage element by weight

Element	C	Si	S	P	Mn	Ni	Cr	Mo
Value ¹	0.275	0.198	0.0157	0.0071	0.457	4.01	1.119	0.213
Uncertainty ²	0.004	0.004	0.0005	0.0002	0.005	0.03	0.009	0.003

Element	Cu	V	Ti	W	Sn	Al	As	N
Value ¹	0.195	0.0029	0.0012	0.0015	0.0101	0.004	0.0068	0.0087
Uncertainty ²	0.003	0.0003	0.0002	0.0001	0.0003	0.001	0.0005	0.0003

Definitions

- ¹ The assigned values are the present best estimates of the true content for each element. Each value is a panel consensus, based on the averaged results of an interlaboratory testing programme, detailed on page 3.
- ² The uncertainty values are generated from the 95% confidence interval derived from the wet analysis results, in combination with a statistical assessment of the homogeneity data, as described on page 2.

Certified by:

MBH ANALYTICAL LIMITED _____

on 9th March 2016

C Eveleigh

Method of Preparation

This reference material was produced from commercial bar to BS970: 835M30. The steel was arc-furnace melted and vacuum degassed, prior to continuous casting and hot-rolling to final dimension.

Sampling

Samples for homogeneity checks and milled samples for chemical analysis were taken from multiple positions within the batch. At least 10% of all discs were taken for homogeneity checking.

Homogeneity

The samples were checked for lateral and batch uniformity using an optical emission spectrometer.

Using the meaned data from each surface, standard deviation values were derived for each element as an indicator of any non-homogeneity (as determined for the specific sample size taken by the spectrometer).

Chemical Analysis

Analysis was carried out on millings taken from samples representative of the product. It was performed by a panel of laboratories mostly operating within the terms of EN ISO/IEC 17025 - 2005, using documented standard reference methods and validated by appropriate reference materials.

The individual values listed overpage are the average of each analyst's results.

Estimation of Uncertainties

Each element certified has been analysed by several laboratories, and 95% half-width confidence intervals ($C_{(95\%)}$) for the resultant mean values have been derived by the method shown on page 3.

As a separate exercise, the degree of non-homogeneity of the batch for each element has been quantified by a programme of non-destructive application testing, discussed above.

The final certified uncertainty for each element has been derived by combining these two factors, using the square-root of the summed squares.

Traceability

Much of the analytical work performed to assess this material has been carried out by laboratories with proven competence, as indicated by their accreditation to ISO 17025. It is an implicit requirement for this accreditation that analytical work should be performed with due traceability, via an unbroken chain of comparisons, each with stated uncertainty, to primary standards such as the mole, or to nationally- or internationally-recognised reference materials. In addition, some of the results derived as part of this testing programme have traceability to NIST standards, as part of the analytical calibration or process control.

Usage

Intended use: With optical emission and X-ray fluorescence spectrometers.

Recommended method of use: Steels are generally prepared by milling, turning or grinding. However, users are recommended to follow the calibration and sample preparation procedures specified by the relevant instrument manufacturer. Preparation should be the same for reference materials and the samples for test.

A minimum of five consistent replicate analyses is recommended to provide the necessary sample size. Users are advised to check against possible bias between reference materials and production samples due to differences in metallurgical history, and be aware of possible inter-element effects.

Analytical Data

Percentage element by weight

Sample	C	Si	S	P	Mn	Ni	Cr	Mo
1	0.2629	0.1840	0.0145	0.0067	0.4458	3.946	1.098	0.2053
2	0.2660	0.1865	0.0147	0.0067	0.4460	3.950	1.099	0.2077
3	0.2692	0.1897	0.0148	0.0069	0.4507	3.960	1.101	0.2100
4	0.2720	0.1940	0.0149	0.0069	0.4511	3.987	1.102	0.2105
5	0.2721	0.1950	0.0152	0.0069	0.4513	3.991	1.104	0.2110
6	0.2750	0.1974	0.0153	0.0071	0.4520	3.998	1.114	0.2110
7	0.2750	0.1980	0.0159	0.0071	0.4578	4.019	1.121	0.2130
8	0.2763	0.1984	0.0160	0.0072	0.4580	4.020	1.121	0.2138
9	0.2776	0.2005	0.0161	0.0072	0.4586	4.025	1.124	0.2140
10	0.2780	0.2010	0.0162	0.0073	0.4590	4.033	1.124	0.2155
11	0.2788	0.2015	0.0162	0.0073	0.4605	4.052	1.128	0.2161
12	0.2790	0.2030	0.0162	0.0073	0.4640	4.053	1.133	0.2165
13	0.2805	0.2045	0.0164	0.0075	0.4652	4.063	1.138	0.2170
14	0.2820	0.2054	0.0164		0.4726		1.140	0.2215
15		0.2093	0.0165				1.143	
Mean	0.2746	0.1979	0.0157	0.0071	0.4566	4.007	1.119	0.2131
Std Dev	0.0056	0.0071	0.0007	0.0002	0.0076	0.039	0.016	0.0042
C (95%)	0.0032	0.0039	0.0004	0.0001	0.0044	0.024	0.009	0.0024

Sample	Cu	V	Ti	W	Sn	Al	As	N
1	0.1890	0.0020	0.0007	0.0013	0.0092	0.0029	0.0055	0.0081
2	0.1891	0.0025	0.0007	0.0014	0.0092	0.0029	0.0061	0.0084
3	0.1900	0.0026	0.0009	0.0014	0.0093	0.0032	0.0064	0.0085
4	0.1914	0.0027	0.0010	0.0015	0.0100	0.0034	0.0064	0.0087
5	0.1919	0.0027	0.0010	0.0016	0.0100	0.0038	0.0065	0.0088
6	0.1925	0.0027	0.0010	0.0016	0.0101	0.0047	0.0065	0.0088
7	0.1930	0.0028	0.0011	0.0016	0.0102	0.0048	0.0067	0.0090
8	0.1937	0.0028	0.0013	0.0017	0.0102	0.0049	0.0068	0.0091
9	0.1960	0.0029	0.0013	0.0018	0.0104	0.0050	0.0069	0.0091
10	0.1968	0.0030	0.0014		0.0104	0.0051	0.0070	
11	0.1969	0.0030	0.0015		0.0106	0.0053	0.0072	
12	0.1972	0.0032	0.0015		0.0108	0.0056	0.0080	
13	0.2001	0.0032	0.0016		0.0109		0.0081	
14	0.2017	0.0033						
15	0.2030	0.0034						
Mean	0.1948	0.0029	0.0012	0.0015	0.0101	0.0043	0.0068	0.0087
Std Dev	0.0045	0.0004	0.0003	0.0002	0.0006	0.0010	0.0007	0.0003
C (95%)	0.0025	0.0002	0.0002	0.0001	0.0003	0.0006	0.0004	0.0003

Note: $C_{(95\%)}$ is the 95% half-width confidence interval derived from the equation:

$$C_{(95\%)} = (t \times SD) / \sqrt{n}$$

where n is the number of available values, t is the Student's t value for n-1 degrees of freedom, and SD is the standard deviation of the test results.

Participating Laboratories

Exova Ltd	Middlesbrough, England	UKAS accreditation 0239
Sheffield Assay Office	Sheffield, England	UKAS accreditation 0012
Metals Technology (Testing) Ltd	Sheffield, England	UKAS accreditation 0963
Universal Scientific Laboratory Pty Ltd	Milperra, NSW, Australia	NATA accreditation 0492
Genitest, Inc	Montreal, Canada	PRI accreditation 123077
Shanghai Jinyi Test Technology Co	Shanghai, China	CNAL accreditation 0783
Shandong Metallurgical & Science Research	Jinan, Shandong, China	CNAS accreditation 1461
Raghavendra Spectromet Laboratory	Bangalore, India	NABL accreditation 0371
Bureau Veritas CPS Pvt	Chennai, India	NABL accreditation 0025
TCR Engineering Services Ltd	Mumbai, India	NABL accreditation 0367
Tec-Eurolab	Campogalliano, Italy	ACCREDIA accreditation 52
Instytut Metalurgii Zelaza	Gliwice, Poland	PCA accreditation AB554
Mineral & Metallurgical Laboratories	Bangalore, India	
Coleshill Laboratories Ltd	Birmingham, England	
AMG Superalloys UK Ltd	Rotherham, England	
Analyticka Laborator Lithea, sro	Brno, Czech Republic	

Note: to achieve the above accreditation (UKAS, NATA, etc), test houses are required to demonstrate conformity to the general requirements of EN ISO/IEC 17025.

Analytical Methods Used

ELEMENT	RESULT No. & METHOD			
	ICP-AES	FAAS		OTHER
Carbon	-	-	all	combustion (IR or volumetric detection)
Silicon	1, 3, 4, 6, 8, 11, 14, 15	-	2, 7, 9, 13	gravimetric (perchloric acid)
Sulfur	2, 11	-	5, 10, 12	photometric (molybdenum blue)
Phosphorus	2-4, 6, 7, 9, 12, 13	-	1, 3-10, 12-15	combustion (IR or volumetric detection)
Manganese	1, 3-5, 9, 10, 13, 14	2, 11	1, 8, 11	volumetric (alkalimetric)
Nickel	3, 5, 7, 11-13	1, 2	5, 10	photometric (molybdenum blue)
Chromium	2, 3, 5-7, 11-13, 15	9, 14	6, 8	volumetric (arsenite)
Molybdenum	2, 4, 5, 8, 10, 12-14	1, 3, 11	7, 12	photometric (periodate)
Copper	1, 2, 4-8, 11, 12, 14	10, 13	4, 9, 10	gravimetric (dimethyl glyoxime)
Vanadium	1, 3-8, 11-15	2, 9, 10	6, 8	photometric (dimethyl glyoxime)
Titanium	1, 2, 4-7, 9-12	3, 8, 13	1	photometric (diphenyl carbazide)
Tungsten	1-7, 9	8	4, 8, 10	volumetric (ferrous ammonium sulfate)
Tin	1-3, 5-7, 10-13	4, 9	6, 7, 9	photometric (thiocyanate)
Aluminium	3-6, 9-11	1, 8, 12	3, 9	photometric (BCO)
Arsenic	1-6, 8-11, 13	7, 12	15	volumetric (thiosulfate)
Nitrogen	-	-	8	gravimetric (oxide)
			2, 7	photometric (chrome azurol S)
			1, 2, 6-8	inert gas fusion (thermal conductivity)
			3, 5	photometric (nessler's reagent)
			4, 9	volumetric (hydrochloric acid)

Notes

This Certified Reference Material has been produced and certified in accordance with the requirements of ISO Guide 34-2009, ISO Guide 31-2015 and ISO Guide 35-2006, taking into account the requirements of the ISO Guide to the Expression of Uncertainty in Measurement (GUM).

This certification is applicable to the whole of the disc. However, in accordance with normal practice for emission spectrometry, it is appropriate to avoid usage of the central portion, ~8 mm diameter.

This material will remain stable indefinitely, provided adequate precautions are taken to protect it from cross-contamination, extremes of temperature and atmospheric moisture. All testing records will be retained for a period of 20 years from the date of this certificate. Technical support for this certification will therefore expire in March 2036, although we reserve the right to make changes as issue revisions, in the intervening period.

This material is also available in the form of chippings.

The analysis and certification of this product were supervised by C Eveleigh, PhD, Technical Director, MBH Analytical Ltd.

The material to which this certificate of analysis refers is supplied subject to our general conditions of sale.